



## KIPP Clamping levers ergonomic, external thread Black Steel 5.8/plastic Zinc plated M10X25

Article number	58140.100.025
Brand	-
UBB	500689997590
UNSPSC	31162807
EAN	4059245206759
PKG. of 5	Full Box Only

### Technical Parameters

Class	5.8
Color	Black
D1_MM	30.5mm
Material	Steel/plastic
Surface treatment	Zinc plated
Thread	Metric thread

Info	Material: Handle: Hard components reinforced plastic, toothed ring die- cast zinc. Soft components thermoplastic elastomeric. Steel parts: grade 5.8.Version: Steel parts zinc plated, blue passivated.Note: The colour combinations graphite black RAL 9011 (hard components) and black grey RAL 7021 (soft components) are supplied as standard. The soft components ensure
------	---

### Standards

a non-slip grip of the operating part. The closed design offers sufficient protection against dirt. The design was especially developed for ergonomic gripping requirements. The push button improves disengagement and allows the handle to be easily used.

## Technical Specification

A	88.5
A1	99.5
B	20
D	16
D1	30.5
H	55.6
H2	37.3
H3	76.5
H4	81
H1	10
Number of teeth	22
L	25
X	10

## Technical Drawing

