



## KIPP Indexing plungers, high, lockout type, without locknut Metric fine thread Stainless steel 1.4305, hardened pin, plastic grip 5MM

Article number	58581.000.005
Brand	-
UBB	500689867561
UNSPSC	31162807
EAN	4059245013340
PKG. of 3	Full Box Only

### Technical Parameters

D1_MM	10mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread
Info	Material: Stainless steel. Threaded sleeve 1.4305 Indexing pin 1.4034 Mushroom knob black grey thermoplastic. Version: Indexing pin hardened, ground and bright. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. The lockout types are recommended for applications in

### Standards

which the pin is disengaged over extended periods and should be prevented from springing back..

### Technical Specification

D	5
D1	10
D2	21
F1 = springiness beginning in N	5
F2 = springiness end in N	12
F x 30°	1.3
H	5
L1	17
L2	7
L3	15
L	47
P	1
SW1	13

### Technical Drawing

