



**KIPP Indexing plungers,
high, lockout type, without
locknut Metric fine thread
Stainless steel 1.4305,
hardened pin, plastic grip
10MM**

Article number	58581.000.010
Brand	-
UBB	500689867801
UNSPSC	31162807
EAN	4059245013371
PKG. of 1	Full Box Only

Technical Parameters

D	10
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread

Standards

Info	<p>Material: Stainless steel. Threaded sleeve 1.4305 Indexing pin 1.4034 Mushroom knob black grey thermoplastic. Version: Indexing pin hardened, ground and bright. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. The lockout types are recommended for applications in</p>
------	--

which the pin is disengaged over extended periods and should be prevented from springing back..

Technical Specification

D	10
D ₁	M20
D ₂	33
F1 = springiness beginning in N	20
F2 = springiness end in N	34
F x 30°	2.8
H	10
L ₁	28
L ₂	12
L ₃	25
L	80
P	1.5
SW1	22

Technical Drawing

