



**KIPP Indexing plungers,
high, lockout type, without
locknut Metric fine thread
Stainless steel 1.4305, pin
not hardened, plastic grip
8MM**

Article number	58585.000.008
Brand	-
UBB	500689869393
UNSPSC	31162807
EAN	4059245013555
PKG. of 2	Full Box Only

Technical Parameters

D1_MM	16mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread
Info	Material: Stainless steel. Threaded sleeve 1.4305 Indexing pin 1.4305 Mushroom knob black grey thermoplastic.Version: Indexing pin not hardened, ground and bright.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. The lockout types are recommended for applications in

Standards

which the pin is disengaged over extended periods and should be prevented from springing back..

Technical Specification

D	8
D1	16
D2	33
F1 = springiness beginning in N	15
F2 = springiness end in N	35
F x 30°	2.3
H	8
L1	26
L2	10
L3	23
L	74
P	1.5
SW1	19

Technical Drawing

