



KIPP Indexing plungers with threaded pin, with locknut Metric fine thread Steel 5.8, hardened pin Black oxide 3MM

Article number	58589.000.003
----------------	---------------

Brand	-
-------	---

UBB	500689871274
-----	--------------

UNSPSC	31162807
--------	----------

EAN	4059245014460
-----	---------------

PKG. of 5	Full Box Only
-----------	---------------

Technical Parameters

D	3
---	---

Class	5.8
-------	-----

Material	Steel
----------	-------

Surface treatment	Black Oxide
-------------------	-------------

Thread	Metric fine thread
--------	--------------------

Info	Material: Steel grade 5.8. Version: Indexing pin hardened, ground, black oxidized. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been disengaged. Special grips can be fitted on the projecting threaded pin. This pin is also suitable for automatic actuation e.g. program controlled pneumatic cylinder or by remote control
------	--

Standards

using Bowden cables.

FABORY
OF COURSE.

Technical Specification

D	3
D ₁	M6
D ₂	M2
F ₁ = springiness beginning in N	4.5
F ₂ = springiness end in N	10
F x 30°	0.8
H	3.5
L ₁	12
L ₂	5
L ₃	3.5
L ₄	10
L	24
P	0.75
SW1	8
SW2	10

Technical Drawing

