



**KIPP Indexing plungers
without collar, with locknut
Metric fine thread Steel 5.8,
hardened pin Black oxide
10MM**

Article number	58601.000.010
Brand	-
UBB	500689879525
UNSPSC	31162807
EAN	4059245015818
PKG. of 4	Full Box Only

Technical Parameters

Class	5.8
D1_MM	20mm
Material	Steel
Surface treatment	Black Oxide
Thread	Metric fine thread

Info Material: Steel grade 5.8. Mushroom knob black grey thermoplastic.Version: Indexing pin hardened, ground, black oxidized.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. A screw-in washer can be supplied to help screw in the indexing plungers. The washer is slid beneath

Standards

FABORY the disengaged mushroom knob so that the carrier pins engage in the slot.

Technical Specification

D	10
D1	20
D2	33
F1 = springiness beginning in N	15
F2 = springiness end in N	34
F x 30°	2.8
H	10
L1	40
L2	24
L	74
P	1.5
SW	30

Technical Drawing

