



**KIPP Indexing plungers
without collar, high, with
locknut Metric fine thread
Stainless steel 1.4305,
hardened pin 10MM**

Article number	58609.000.010
Brand	-
UBB	500689884483
UNSPSC	31162807
EAN	4059245015924
PKG. of 2	Full Box Only

Technical Parameters

D1_MM	20mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread
Info	Material: Stainless steel threaded sleeve 1.4305 Indexing pin 1.4034 Mushroom knob black grey thermoplastic.Version: Indexing pin hardened, ground and bright.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. A screw-in washer can be supplied to help screw in the indexing plungers.

Standards

The washer is slid beneath the disengaged mushroom knob so that the carrier pins engage in the slot.

Technical Specification

D	10
D1	20
D2	33
F1 = springiness beginning in N	20
F2 = springiness end in N	34
F x 30°	2.8
H	10
L1	40
L2	30
L	80
P	1.5
SW	30

Technical Drawing

