



KIPP Ball lock pins self-locking, form A Stainless steel/plastic 10X60MM

Article number	58648.100.060
Brand	-
UBB	500689912102
UNSPSC	31162807
EAN	4059245022199
PKG. of 2	Full Box Only

Technical Parameters

D1_MM	10mm
Material	Stainless steel/ plastic
Info	Material: Grip and push button thermoplastic. Metal parts stainless steel.Version: Grip black. Push button traffic red. Steel parts bright.Note: Ball lock pins are used for quick and easy fastening and joining of parts and work pieces. The two balls are disengaged by pressing the push button and the pin can be slipped into holes in the work pieces. Release the button to lock the balls and secure the connection. Form A is suitable for applications where high demands and precision are required. Shearing

Standards

force double shear
(F) = S · τ aB
max.Characteristics:
Form A: Pin ground,
metal collar, high
axial pull-out
force.Accessories:
Safety spiral cable
K0367.10200
Retaining cable with
loop K0367. Key
ring K0367.15/19/23
Bushing for ball lock
pins K0724.

Technical Specification

D 47

D2	12
----	----

L1	9
----	---

L	60
---	----

Shearing force (double shear), max. (kN) 60

Technical Drawing

