



**KIPP Indexing plungers
without collar with extended
pin with locknut Metric
fine thread Stainless steel
1.4305, pin not hardened,
plastic grip 3MM**

Article number	58693.000.003
Brand	-
UBB	500690020416
UNSPSC	31162807
EAN	4059245015658
PKG. of 4	Full Box Only

Technical Parameters

D1_MM	6mm
Material	Stainless steel
Material technical	1.4305
Thread	Metric fine thread
Info	Material: Stainless steel threaded sleeve 1.4305 Indexing pin 1.4305 Mushroom knob black grey thermoplastic.Version: Indexing pin not hardened, ground and bright.Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. A screw-in washer can be supplied to help screw in the

Standards

indexing plungers.
The washer is
slid beneath
the disengaged
mushroom knob so
that the carrier pins
engage in the slot.

Technical Specification

D	3
D1	6
D2	14
F1 = springiness beginning in N	4.5
F2 = springiness end in N	12
F x 30°	0.8
H	5
L1	17
L2	11
L	33
P	0.75
SW	10

Technical Drawing

