



**KIPP Indexing plungers,
lockout type, without locknut
Steel, plastic grip Zinc plated
4MM**

Article number	58739.000.004
Brand	-
UBB	500690059521
UNSPSC	31162807
EAN	4059245204830
PKG. of 10	Full Box Only

Technical Parameters

D1_MM	6mm
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	Material: Steel. Threaded sleeve 1.0718. Indexing pin 1.4305. Mushroom knob black grey thermoplastic.Version: Indexing pin not hardened. Threaded sleeve zinc plated, blue passivated. Indexing pin bright.Note: This article is a cost- efficient alternative to the existing indexing plungers. It is suitable for applications which require less precision. The max. tightening torque should be observed when assembling.

Standards

D	4
D1	6
D2	14
F1 = springiness beginning in N	6
F2 = springiness end in N	12
F x 30°	1
H	4
L1	15
L2	6
L3	13
L	36
SW1	6
Tightening torque (max.) (Nm)	2

