



**KIPP Indexing plungers,
short, non-lockout type,
with locknut Stainless steel
1.4305, pin not hardened,
plastic grip 8MM**

| | |
|----------------|---------------|
| Article number | 58750.000.008 |
| Brand | - |
| UBB | 500690065395 |
| UNSPSC | 31162807 |
| EAN | 4059245205417 |
| PKG. of 5 | Full Box Only |

Technical Parameters

| | |
|--------------------|---|
| D1_MM | 16mm |
| Material | Stainless steel |
| Material technical | 1.4305 |
| Thread | Metric thread |
| Info | Material: Threaded sleeve 1.4305. Indexing pin 1.4305. Mushroom knob black grey thermoplastic.Version: Indexing pin not hardened, stainless steel parts bright.Note: This article is a cost-efficient alternative to the existing indexing plungers. It is suitable for applications which require less precision. The max. tightening torque should be observed when assembling. |

Standards

| | |
|------------------------------------|-----|
| D | 8 |
| D1 | 16 |
| D2 | 33 |
| F1 = springiness beginning in N | 6 |
| F2 = springiness end in N | 13 |
| F x 30° | 2.3 |
| H | 8 |
| L1 | 12 |
| L2 | 10 |
| L | 54 |
| SW1 | 19 |
| SW2 | 24 |
| Tightening torque (max.) (Nm) | 20 |

