



KIPP Indexing plungers for thin-walled parts, lockout type Metric fine thread Steel 5.8, hardened pin, plastic grip Black oxide 5MM

Article number	58767.000.005
Brand	-
UBB	500690077358
UNSPSC	31162807
EAN	4059245012305
PKG. of 4	Full Box Only

Technical Parameters

Class	5.8
D1_MM	10mm
Material	Steel
Surface treatment	Black Oxide
Thread	Metric fine thread

Info Material: Steel grade 5.8 Mushroom knob black grey thermoplastic.Version: Indexing pin hardened, ground, black oxidized.Note: These indexing plungers are especially well-suited for assembly in thin-walled parts. Indexing plungers are used where any change in locking position due to lateral forces should be prevented. A new locking position can be set only after the pin has been manually disengaged. The

Standards

lockout type is recommended for applications where the locking pin should remain disengaged for an extended period and be prevented from springing back.

Technical Specification

D	5
D1	10
D2	28
D3	10
F1 = springiness beginning in N	6
F2 = springiness end in N	15
F x 30°	1.3
H	5
L1	11.5
L2	13
L3	10.5
L	46.5
P	1
SW1	17
SW2	14

Technical Drawing

