

Dormer Jobber drill A002
DIN 338 HSS Blanc/TiN
5/16In



Article number	6R381746
Brand	-
UBB	500631023420
UNSPSC	23241639
EAN	7320760351192
PKG. of 10	Full Box Only

Technical Parameters

Total length	117
Holding system	Cylindrical plug-in axle
Cutting length	75
Cutting material	HSS
Shank shape	Cylindrical
Spiral drill	Yes

Standards