

SPIT Chemical fixing threaded rod Steel Zinc plated M8



Article number	70636.080.001
Brand	-
UBB	500503079047
UNSPSC	31161601
EAN	8715494468978
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M8
Length	110 mm
Material	Steel
Approval	ETA Option 7
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	Maxima

Info Full boxes only.M8 - M16 are supplied including setting toolFor a complete chemical anchor, the capsule and threaded stud (incl. nut and washer), have to be ordered separately.For further technical data the approval is available on request.

Standards

Technical Specification

Allowable load (kN)	5.3
d-D	M8
Depth of drilled hole to deepest point (homin.-hmax.)	80

Technical Drawing

Diameter of
clearance hole in the
fixture (df)

9

Edge distance (Ccr,
N), characteristic

80

Effective anchorage
depth (hef.min.-
hef.max.)

80

L (mm)

110

Minimal edge
distance (Cmin.)

40

Minimal spacing
(Smin.)

40

Minimal thickness
of concrete element
(hmin.)

110

Nominal diameter of
drill bit (do)

10

Spacing (Scr, N),
characteristic

160

Thickness of the
fixture

15

Tightening torque
(Nm)

10

