

SPIT Chemical fixing threaded rod Steel Zinc plated M10



Article number	70636.100.001
Brand	-
UBB	500503079120
UNSPSC	31161601
EAN	8715494468985
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M10
Length	130 mm
Material	Steel
Approval	ETA Option 7
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	Maxima

Info Full boxes only.M8 - M16 are supplied including setting toolFor a complete chemical anchor, the capsule and threaded stud (incl. nut and washer), have to be ordered separately.For further technical data the approval is available on request.

Standards

Technical Specification

Allowable load (kN)	8.3
d-D	M10
Depth of drilled hole to deepest point (homin.-hmax.)	90

Technical Drawing

Diameter of
clearance hole in the
fixture (df)

Edge distance (Ccr,
N), characteristic

Effective anchorage
depth (hef.min.-
hef.max.)

L (mm)

Minimal edge
distance (Cmin.)

Minimal spacing
(Smin.)

Minimal thickness
of concrete element
(hmin.)

Nominal diameter of
drill bit (do)

Spacing (Scr, N),
characteristic

Thickness of the
fixture

Tightening torque
(Nm)

12

90

90

130

45

45

120

12

180

25

20

