

SPIT Chemical fixing threaded rod Stainless steel A4 M16



Article number	70646.160.001
Brand	-
UBB	500503080847
UNSPSC	31161601
EAN	3439510524404
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M16
Length	190 mm
Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread
Type no.	Maxima
Info	M8 - M16 are supplied including setting toolFor a complete chemical anchor, the capsule and threaded stud (incl. nut and washer), have to be ordered separately.For further technical data the approval is available on request.

Standards

Technical Specification

Allowable load (kN)	19.8
d-D	M16
Depth of drilled hole to deepest point (homin.-hmax.)	125

Technical Drawing

Diameter of
clearance hole in the
fixture (df) 18

Edge distance (Ccr,
N), characteristic 125

Effective anchorage
depth (hef.min.-
hef.max.) 125

L (mm) 190

Minimal edge
distance (Cmin.) 65

Minimal spacing
(Smin.) 65

Minimal thickness
of concrete element
(hmin.) 160

Nominal diameter of
drill bit (do) 18

Spacing (Scr, N),
characteristic 250

Thickness of the
fixture 40

Tightening torque
(Nm) 60

