

SPIT Chemical fixing threaded rod Stainless steel A4 M24



Article number	70646.240.001
Brand	-
UBB	500503081001
UNSPSC	31161601
EAN	3439510524701
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	300 mm
Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread
Type no.	Maxima
Info	M8 - M16 are supplied including setting toolFor a complete chemical anchor, the capsule and threaded stud (incl. nut and washer), have to be ordered separately.For further technical data the approval is available on request.

Standards

Technical Specification

Allowable load (kN)	38
d-D	M24
Depth of drilled hole to deepest point (homin.-hmax.)	210

Technical Drawing

Diameter of
clearance hole in the
fixture (df)

26

Edge distance (Ccr,
N), characteristic

210

Effective anchorage
depth (hef.min.-
hef.max.)

210

L (mm)

300

Minimal edge
distance (Cmin.)

105

Minimal spacing
(Smin.)

105

Minimal thickness
of concrete element
(hmin.)

300

Nominal diameter of
drill bit (do)

28

Spacing (Scr, N),
characteristic

420

Thickness of the
fixture

64

Tightening torque
(Nm)

200

