



SPIT Anchor bolt Stainless steel A4 8-20

Article number	70835.080.020
Brand	-
UBB	500511029406
UNSPSC	31162101
EAN	8715494224086
PKG. of 100	Full Box Only

Technical Parameters

Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread

Info

do= Nominal diameter of drill bit.Min. td= Recommended drilling depth.hef= Effective anchorage depth.tfix= Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account.Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Standards

Technical Specification

d-D	M8
do	8
hef	34
kN	1.7
L (mm)	70
tfix	20