



Brady Repositionable Vinyl Cloth Label B33C-312-498

Article number	7Y597587
Brand	-
UBB	500671631421
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Color	White
Width (mm)	7.92
Adhesive component	Repositionable Rubber
Basic material	Vinyl Cloth
Brady material number	B-498
Legend	Repositionable Vinyl Cloth Labels for BBP33/i3300 Printers
Max. service temp. °C	80 °C
Min. service temp. °C	-40 °C
Print technology	Thermal Transfer
Printer compatibility	BBP33
Product regulations	IMO
Ribbon series	B30-R6200
Compliance	UL Recognised
Performance characteristics	Abrasion Resistance;Low Temperature Resistance;Removable
Industry	Electrical and Voice &

Standards

Datacommunication
identification

FABUKY
Content (pcs) **OF COURSE.**
SETTING THE STANDARD

Finish	Semi gloss
Finish	Halbglanz
Finish	Semi lucios
Finish	Półmatowy
Finish	Semi brillo
Finish	Semi-brillant
Finish	Semi lesk
Finish	Zijdeglans
Finish	Fél fényes
Finish	Semi brilho
Finish	Semi lesk
Application method	Electrical & Automation Identification; Repositionable Terminal Block Marking
Length (mtr)	25.91
Model	CleanLift
Thickness	0.185
Type nr.	B-498
Weight (g)	499