



Metabo Straight grinders DG 25 SET

Article number	7Z033964
Brand	-
UBB	500658589170
UNSPSC	42272202
EAN	4007430228918
PKG. of 1	Full Box Only

Technical Parameters

Rotational speed	25000
Max. operation pressure	6.2
Tool insertion	6
Air inlet device-sided	R 1/4 inch
Model	DG 25 Set
Type	BH_NF_inh_03_EN

Standards