



## Bosch Jigsaw GST150CE

|                |               |
|----------------|---------------|
| Article number | B4500.000.050 |
| Brand          | -             |
| UBB            | 500571224889  |
| UNSPSC         | 27111508      |
| EAN            | 3165140463720 |
| PKG. of 1      | Full Box Only |

### Technical Parameters

|                                                            |     |
|------------------------------------------------------------|-----|
| Stroke                                                     | 26  |
| Voltage                                                    | 230 |
| Nominal power consumption                                  | 780 |
| Machine weight                                             | 2.6 |
| Cutting depth in wood                                      | 150 |
| No-load stroke rate                                        | 500 |
| Max. material thickness in aluminium 250 N/mm <sup>2</sup> | 20  |
| Max. material thickness in steel 400 N/mm <sup>2</sup>     | 10  |

### Standards