



Stahlwille Sockets 50 30 MM

Article number	G0365.300.001
Brand	-
UBB	203122108731
UNSPSC	27111704
EAN	4018754005383
PKG. of 1	Full Box Only

Technical Parameters

Drive size	1/2
Non spark	No
Total length (mm)	45
Size (mm)	30
Type	12 point
Type nr.	50

Info

1/2" connection.
Metric sizes: DIN 3124/ISO 2275-1, E DIN EN 3709 ASME B 107.5M.
American sizes: ASME B 107.1 Fed. Spec. GGG-W-641, SAE AS 954-E (test loads). HPQ-high performance steel, Chrome plated.

Standards

DIN 3124