



Power combination pliers length 200 mm chrome- plated dip-insulated VDE KNIPEX

Article number	K1002.700.200
Brand	-
UBB	240102237825
UNSPSC	27112139
EAN	4003773022299
PKG. of 1	Full Box Only

Technical Parameters

Insulated	Yes
Shape	Straight
Surface protection	Chromium-plated
Length	200
Isolation protection 1000 V	Yes
Cut sticking out	Yes
Material	Steel
Strip range diameter	2.8 - 2.8
Strip range cross- section	25 - 25
Grip design	2-components
Handle cover	Other
Forged	Yes
VDE tested	Yes

Standards