



IMPACT WRENCH 1 MI-38ELR

Article number	MI-38ELRTO
Brand	-
UBB	500619058521
UNSPSC	27112713
EAN	8717981148325
PKG. of 1	Full Box Only

Technical Parameters

Max. operation pressure	6.3
Tool insertion	1 inch
Idle rotational speed	4500
Max. loosening torque	1800
Max. tightening torque	1800
Impulse driver	Yes
Max. thread size (metric)	36

Standards