



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Steel Plain Gr.B7 -
Gr.2H 1.3/4X540 (21.1/4)**

Article number	PIMI0444540
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.3/4 Inch
Length	540 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Plain

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	540
--------	-----

Technical Drawing

FABORY

