



Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Steel Zinc plated Gr.B7 - Gr.2H 5/8X130 (5.1/8)

Article number	PIMI1158130
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	130 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	130
--------	-----

Technical Drawing

FABORY

