



**Studbolt with 2 heavy  
hexagon nuts ASTM A193/  
A194 Steel Zinc plated  
Gr.B7 - Gr.2H 2 Inch X1100  
(43.5/16)**

Article number	PIMI1509100
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	2 Inch
Length	1100 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASTM	A193/A194
------	-----------

**Technical Specification**

L (mm)	1100
--------	------

**Technical Drawing**

# FABORY

