



**Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Steel Zinc plated yellow passivated Gr.B7 - Gr.2H 1.3/8X255 (10)**

Article number	PIMI2349255
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	1.3/8 Inch
Length	255 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated yellow passivated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASTM	A193/A194
------	-----------

**Technical Specification**

L (mm)	255
--------	-----

**Technical Drawing**

FABORY

