



**Studbolt with 2 heavy  
hexagon nuts ASTM  
A193/A194 Steel Hot dip  
galvanized Gr.B7 - Gr.2H  
3/4X150 (6)**

|                |               |
|----------------|---------------|
| Article number | PIMI4191150   |
| Brand          | -             |
| UBB            | 500641397491  |
| UNSPSC         | 00000000      |
| EAN            |               |
| PKG. of 1      | Full Box Only |

**Technical Parameters**

|                   |                    |
|-------------------|--------------------|
| Diameter          | 3/4 Inch           |
| Length            | 150 mm             |
| Class             | Gr.B7 - Gr.2H      |
| Material          | Steel              |
| Surface treatment | Hot dip galvanized |

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

|      |           |
|------|-----------|
| ASTM | A193/A194 |
|------|-----------|

**Technical Specification**

|        |     |
|--------|-----|
| L (mm) | 150 |
|--------|-----|

**Technical Drawing**

FABORY

