

ST+2N A193-B7/A194-2H HDG 7/8X135

| | |
|-------------|---------------|
| Article No. | PIMI4222135 |
| Brand | - |
| UBB | |
| UNSPSC | |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---|

Standards

| | |
|------|---------------|
| ASTM | A193/A194 |
| ASME | B16.5/B18.2.2 |
| BS | ≈4882 |

Technical Specification

Technical Drawing