



**Studbolt with 2 heavy
hexagon nuts ASTM
A193/A194 Steel Hot dip
galvanized Gr.B7 - Gr.2H
1.5/8X300 (11.3/4)**

Article number	PIMI4412300
Brand	-
UBB	500635794166
UNSPSC	00000000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.5/8 Inch
Length	300 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Hot dip galvanized

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	300
--------	-----

Technical Drawing

FABORY

