



**Studbolt with 2 heavy
hexagon nuts ASTM
A193/A194 Steel Hot dip
galvanized Gr.B7 - Gr.2H
1.7/8X350 (13.3/4)**

| | |
|----------------|---------------|
| Article number | PIMI4476350 |
| Brand | - |
| UBB | 500635794240 |
| UNSPSC | 00000000 |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|--------------------|
| Diameter | 1.7/8 Inch |
| Length | 350 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Surface treatment | Hot dip galvanized |

Info
Tolerances of the total length of the studbolts according to ASME B16.5
Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

| | |
|------|-----------|
| ASTM | A193/A194 |
|------|-----------|

Technical Specification

| | |
|--------|-----|
| L (mm) | 350 |
|--------|-----|

Technical Drawing

FABORY

