



**Studbolt with 2 heavy  
hexagon nuts ASTM A193/  
A194 Steel Zinc bichromated  
Gr.B7M - Gr.2HM 5/8X145  
(5.3/4)**

Article number	PIMJ3158145
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	5/8 Inch
Length	145 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Surface treatment	Zinc bichromated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASTM	A193/A194
------	-----------

**Technical Specification**

L (mm)	145
--------	-----

**Technical Drawing**

# FABORY

