



Studbolt with 2 heavy hexagon nuts ASTM A193/ A194 Steel Zinc bichromated Gr.B7M - Gr.2HM 7/8X155 (6.1/8)

Article number	PIMJ3222155
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	7/8 Inch
Length	155 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Surface treatment	Zinc bichromated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM A193/A194

Technical Specification

L (mm)	155
--------	-----

Technical Drawing

FABORY

