



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Steel Zinc bichromated
Gr.B7M - Gr.2HM 7/8X260
(10.1/4)**

Article number	PIMJ3222260
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	7/8 Inch
Length	260 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Surface treatment	Zinc bichromated

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	260
--------	-----

Technical Drawing

FABORY

