



**Studbolt with 2 heavy
hexagon nuts ASTM
A320/A194 Steel Hot dip
galvanized Gr.L7M - Gr.7M
5/8X115 (4.1/2)**

| | |
|----------------|---------------|
| Article number | PIMO4158115 |
| Brand | - |
| UBB | |
| UNSPSC | |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|--------------------|
| Diameter | 5/8 Inch |
| Length | 115 mm |
| Class | Gr.L7M - Gr.7M |
| Material | Steel |
| Surface treatment | Hot dip galvanized |

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

| | |
|------|-----------|
| ASTM | A320/A194 |
|------|-----------|

Technical Specification

| | |
|--------|-----|
| L (mm) | 115 |
|--------|-----|

Technical Drawing

FABORY

