



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Stainless steel Plain
Gr.B8M Cl.1 - Gr.8M 5/8X95
(3.3/4)**

Article number	PIMPE158095
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	95 mm
Class	Gr.B8M Cl.1 - Gr.8M
Material	Stainless steel
Surface treatment	Plain

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	95
--------	----

Technical Drawing

FABORY

