



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Stainless steel
Plain Gr.B8M Cl.2 - Gr.8M
1.5/8X370 (14.1/2)**

Article number	PIMPF412370
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.5/8 Inch
Length	370 mm
Class	Gr.B8M Cl.2 - Gr.8M
Material	Stainless steel
Surface treatment	Plain

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	370
--------	-----

Technical Drawing

FABORY

