



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Stainless steel Plain
Gr.B8M - Gr.8MA 5/8X100 (4)**

Article number	PIMPG158100
Brand	-
UBB	500647627552
UNSPSC	00000000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	100 mm
Class	Gr.B8M - Gr.8MA
Material	Stainless steel
Surface treatment	Plain

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	100
--------	-----

Technical Drawing

FABORY

