



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Stainless steel Plain
Gr.B8M - Gr.8MA 5/8X130
(5.1/8)**

Article number	PIMPG158130
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	130 mm
Class	Gr.B8M - Gr.8MA
Material	Stainless steel
Surface treatment	Plain

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	130
--------	-----

Technical Drawing

FABORY

