



**Studbolt with 2 heavy  
hexagon nuts ASTM A193/  
A194 Stainless steel Plain  
Gr.B8T Cl.2 - Gr.8T 3/4X210  
(8.1/4)**

Article number	PIMPM191210
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	3/4 Inch
Length	210 mm
Class	Gr.B8T Cl.2 - Gr.8T
Material	Stainless steel
Surface treatment	Plain

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASTM	A193/A194
------	-----------

**Technical Specification**

L (mm)	210
--------	-----

**Technical Drawing**

# FABORY

