



**Studbolt with 2 heavy
hexagon nuts ASTM A193/
A194 Steel Plain Gr.B6 - Gr.6
5/8X205 (8.1/8)**

Article number	PIMPN158205
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	205 mm
Class	Gr.B6 - Gr.6
Material	Steel
Surface treatment	Plain

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASTM	A193/A194
------	-----------

Technical Specification

L (mm)	205
--------	-----

Technical Drawing

FABORY

