



**Studbolt with 2 heavy
hexagon nuts ASTM A453
Superduplex Plain Gr.660 A
1.3/8X295 (11.1/2)**

| | |
|----------------|---------------|
| Article number | PIMSA349295 |
| Brand | - |
| UBB | |
| UNSPSC | |
| EAN | |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|-------------|
| Diameter | 1.3/8 Inch |
| Length | 295 mm |
| Class | Gr.660 A |
| Material | Superduplex |
| Surface treatment | Plain |

| | |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---|

Standards

| | |
|------|------|
| ASTM | A453 |
|------|------|

Technical Specification

| | |
|--------|-----|
| L (mm) | 295 |
|--------|-----|

Technical Drawing

FABORY

