



**Studbolt with 2 heavy
hexagon nuts ASTM B637
Steel Plain NIMONIC 80A 1
Inch X190 (7.1/2)**

Article number	PIMSF254190
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1 Inch
Length	190 mm
Class	NIMONIC 80A
Material	Steel
Surface treatment	Plain

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASTM	B637
------	------

Technical Specification

L (mm)	190
--------	-----

Technical Drawing

FABORY

