



**Studbolt with 2 heavy
hexagon nuts ASME
SA193/SA194 Steel Hot dip
galvanized Gr.B7 - Gr.2H
5/8X100 (4)**

Article number	PIMT4158100
Brand	-
UBB	
UNSPSC	
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	100 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Hot dip galvanized

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	SA193/SA194
------	-------------

Technical Specification

L (mm)	100
--------	-----

Technical Drawing

FABORY

