

## ST+2N SA193-B7/SA194-2H HDG 5/8X100

|             |               |
|-------------|---------------|
| Article No. | PIMT4158100   |
| Brand       | -             |
| UBB         |               |
| UNSPSC      |               |
| EAN         |               |
| PKG. of 1   | Full Box Only |

### Technical Parameters

|      |   |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---|

### Standards

|      |               |
|------|---------------|
| BS   | ≈4882         |
| ASME | B16.5/B18.2.2 |
| ASTM | A193/A194     |

### Technical Specification

### Technical Drawing