

Fabory Jobber drill
Cylindrical DIN 338 RN HSS
Black 10,0 MM



Article number	U0000.100.001
Brand	-
UBB	240201336585
UNSPSC	23241639
EAN	8715494650571
PKG. of 5	Full Box Only

Technical Parameters

Total length	133
Diameter drill	10
Holding system	Cylindrical plug-in axle
Cutting length	87
Suitable for steel	Yes
Cutting material	HSS
Tip angle	118
Shank shape	Cylindrical
Cutting direction	Right
Spiral drill	Yes

Standards

Technical Specification

Technical Drawing

