



**Hexagon socket head cap
screw UNC 1960 series
ASME B18.3 Alloy steel
ASTM A574 Plain #5-40X1/4
ft**

Article number	U07000.012.0025
Brand	-
UBB	500620893429
UNSPSC	31161605
EAN	8717077356757
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.5
Length	1/4 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Info	Marking in accordance with ASTM A574 with manufacturer's identification mark only.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.Warning: electroplating of these products may cause hydrogen
------	--

Standards

ASME	B18.3
------	-------

Technical Specification

A	0.205
H	0.125
J	0.09375
LT (min.)	0.75
Threads per inch	40

Technical Drawing

