



**Hexagon socket head cap
screw UNC 1960 series
ASME B18.3 Alloy steel
ASTM A574 Plain #5-40X5/16
ft**

Article number	U07000.012.0031
Brand	-
UBB	500620893593
UNSPSC	31161605
EAN	8717077356764
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.5
Length	5/16 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Standards

ASME	B18.3
------	-------

Info Marking in accordance with ASTM A574 with manufacturer's identification mark only.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.Warning: electroplating of these products may cause hydrogen

Technical Specification

A	0.205
H	0.125
J	0.09375
LT (min.)	0.75
Threads per inch	40

Technical Drawing

