



**Hexagon socket head cap  
 screw UNC 1960 series  
 ASME B18.3 Alloy steel  
 ASTM A574 Plain #5-40X5/8  
 ft**

Article number	U07000.012.0062
Brand	-
UBB	500620893916
UNSPSC	31161605
EAN	8717077356801
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter (inch)	#5
Driving features	Hexagon socket
Head shape	Cylindrical head
Length (L) (Inch - ft)	5/8
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
TPI	40
Surface treatment	Plain
Thread	Unified National Coarse

**Standards**

ASME	B18.3
------	-------

**Info**  
 Marking in accordance with ASTM A574 with manufacturer's identification mark only. Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems. Warning: electroplating of these products may cause hydrogen

embrittlement. ft =  
fully threaded

**FABORY**  
OF COURSE.

## Technical Specification

A	0,205
H	0.125
J	3/32
L <sub>T</sub> (min.)	0.75
Threads per inch	40

## Technical Drawing

